

Professionally approved products.

Socket Sets

45 Pc Hex/Torx/Spline Driver Bit Set

Material

For Bits: Chrome Molybdenum Steel (S-2)
 Chrome Vanadium for impact socket
 Chrome Vanadium Steel for bit couplers and
 socket adapter

Finish

Chrome plated and Chemical Blackened finish
 of ring for bit couplers and socket adapter
 Phosphate finish for impact sockets
 Sandblasted finish for bits

Hardness

Heat treated to HRC: 56 ~ 62 Degrees for bits
 HRC: 42 ~ 48 Degrees for nut drivers bit
 couplers, impact sockets and for socket
 adapter



[RS Stock No. 213-1011](#)

Contents

7 pc - 30 mm (1-1/4") Standard hex driver bits (10 mm Hexagon shank) sizes: 4, 5, 6, 7, 8, 10 and 12 mm
7 pc - 75 mm (3") Deep hex driver bits (10 mm Hexagon shank) sizes: 4, 5, 6, 7, 8, 10 and 12mm
7 pc - 30 mm (1-1/4") Standard Torx driver bits(10 mm Hexagon shank) sizes: t-20, t-25, t-30, t-40, t-45, t-50 and t-55
7 pc - 75 mm (7 pc) (3") Deep Torx driver bits (10 mm Hexagon shank) sizes: t-20, t-25, t-30, t-40, t-45, t-50 and t-55
5 pc - 30 mm (5 pc) (1-1/4") Standard spline bits (10 mm Hexagon shank) sizes: m-5, m-6, m-8, m-10, m-12
5 pc - 30 mm (5 pc) (1-1/4") Deep spline bits (10 mm Hexagon shank) sizes: m-5, m-6, m-8, m-10, m-12
1 pc - 3/8" dr. To 10 mm Hexagon bit coupler with ring and drill hole
1 pc - 1/2" dr. To 10 mm Hexagon bit coupler with ring and drill hole
1 pc - 1/4" hexagon to 1/2" dr. Socket adapter (length - 72 mm)
4 pc - 1/2" dr. Impact sockets (seal ring with two pin holes of driver end)
 size:17 mm (11/16"), 19 mm (3/4"), 21 mm (13/16") and 23 mm (29/32")

