

Professionally approved products.

Datasheet

6 in Adjustable Spanner with 20mm Jaw Capacity

RS Stock number [817-6573](#)



Specification:

- Material: Chrome vanadium steel (CR-v steel 6150) for adjustable wrenches
- Finish: Phosphate black finish, polish jaw portion with laser scale with logo
- Hardness: Heat treated to HRC: 40 ~ 48

Contents:

1 pc-6" (150mm) wide jaw adjustable wrenches with laser metric scales (overall length - 155 mm, max jaw opening - 19 mm, net weight - 130g)

Remarks:

Torque, hardness and gauges meet din 3117 standard.