

Professionally approved products.

Datasheet

12 inch Adjustable Spanner with 34mm Jaw Capacity

RS Stock number [541-6602](#)



Specification:

Material: Chrome vanadium steel (CR-v steel 6150) for adjustable wrenches

Finish: Phosphate black finish, polish jaw portion with laser scale with logo

Hardness: Heat treated to HRC: 42 ~ 48

Contents:

1 pc-12" (300mm) wide jaw adjustable wrenches with laser metric scales (overall length - 305 mm, max jaw opening - 36 mm, net weight - 700g)

Remarks:

Torque, hardness and gauges meet din 3117 standard.