

Professionally approved products.

Screw Extractors

4pcs 1/2" Dr concentric roller extractors



[RS Stock No. 449-9583](#)

Material: Chrome vanadium steel for socket body medium carbon steel extractor pin high carbon steel for circlip ring.

Finish: Chrome plated finish for socket body zinc plated cover black finish for extractor pin and roller.

Hardness : Heat treated to hrc : 40~46 degree(socket), hrc : 35~40 degree.

Contents :

4 pc - 1/2" driver concentric roller extractors set, 3 legs extract pin, 13/16 " (21mm) hex bolt outside for wrench operated. Fit to use on stud sizes m6, m8, m10 and m12. Knurled on the top central portion of socket body, 1/2" driver end with detent groove and overall length of socket were - m6 & m8 extractor sockets - 63mm, m10 & m12 extractor socket - 74mm, size : m6 x 63 , m8 x 63, m10 x 74 and m12 x 74mm

