

Professionally approved products.

Datasheet

138mm (5 ½ inch) Electricians Shears

RS Stock number [487-224](#)



Specification:

- Material: High carbon molybdenum vanadium stainless steel sheet (aus-8) for shears blade, (scm435) bolt & lock nut and nylon with TPE (thermo plastic elastomer) double injection handle
- Finish: Hollow grounding cutting edge fully polish finish for whole body
- Hardness: vacuum heat treated to HRC: 58~60 (scissors blades)

Contents:

1pc-138mm (5-1/2") heavy -duty electrician's stainless steel utility shears with notch(up to diameter-22.0mm) and red colour(nylon with 35% fiberglass black(TPR) double injection handle (overall length-138mm/5-1/2", micro-serration cutting length-42.0mm(1-5/8") and thickness of blade-3.2mm)

Remark:

Cutting tests for cloth, upholstery, leather