

**Professionally approved products.**

## Datasheet

# Maintenance Terminal Crimping Tool

RS Stock number [499-2313](#)



### Specification

#### Material

- Crimping Jaw and Ratcheting Mechanism - Power die casting chrome molybdenum vanadium steel
- Body - Press molded medium steel sheet
- Automatic Return Spring, Rivets and Spring - Low carbon steel Grip - Polypropylene injection

#### Finish

- Crimping Jaw and Ratcheting Mechanism - Chemical blackened finish
- Body - Black electrical deposition
- Grip - Red colour

#### Hardness

- Crimping Jack - Heat treated to HRC: 40 ~43 degrees
- Body – Heat treated HRC: 42 ~ 48 degrees
- Rivet – Heat treated to HRC: 30 degrees up

### Contents

1 Pc - Standard insulated terminal ratcheting crimping tool (suitable for use on insulated vinyl, Polycarbonate and nylon Red, Blue and Yellow. (wire range from 0.5 mm<sup>2</sup> to 6.0 mm<sup>2</sup>, net weight 480 grams).