

AF26-40-00-13



4 pole, 45 A, non-reversing across the line
contactor with 100-250V AC/DC coil and
no auxiliary contacts



General

Type:	Contactors
Application:	Mainly used for controlling non-inductive or slightly inductive loads (i.e. resistance furnaces...)
T&B UPC:	80432556077
T&B Status:	M
Special Features:	Terminal type: Screw terminals
Amperage Rating:	45 A
Factory Code:	1SBL237201R1300
Number of Poles:	

Dimension Information

Size:	45 x 86 x 101 mm
Height:	86 mm
Width:	45 mm