

Share:



APCRBC123



Description: Genuine APC RBC(TM) are tested and certified for compatibility to restore UPS performance to the original specifications.

Includes : All required connectors , Battery recycling guide , Installation guide , Reusable packaging

Product Overview

Technical Specifications

Documentation

Batteries & Runtime

[Print Technical Specification](#)

Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	--
Expected Battery Life (years)	3 - 5
RBC Quantity	1

Physical

Maximum Height	76mm , 7.6CM
Maximum Width	152mm , 15.2CM
Maximum Depth	203mm , 20.3CM
Net Weight	5.21KG
Shipping weight	5.53KG
Shipping Height	146mm , 14.6CM
Shipping Width	234mm , 23.4CM
Shipping Depth	275mm , 27.5CM

Conformance

Standard warranty	1 year repair or replace
-------------------	--------------------------

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOLI	Available in Documentation tab