

# Product Catalog for professionals

Products > 65389

## 65389 - LED12DBR30/827

GE LED R30

#### This product is no longer manufactured.

• Energy-efficient LED lamps. Long life.



UL damp rated

'n		IED	A I	CIIA	DA	$\cap$ TE	RIST	00
1	1 - F	$\mathbf{u} = \mathbf{K}$	$\Delta$ I	L.HA	R AI		KIN II	

Lamp type	Replacement Lamps - Directional
Bulb	BR30
Base	Medium Screw (E26)
ENERGY STAR® Qualified	Yes
Primary Application	Indoor Floodlight
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Finish	Frost
Bulb Shape	BR30
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	65 W
Lamp Type	LED-BR
Life in Years (NOM)	23 46
Rated Life (NOM)	50000 hrs
· · · · · · · · · · · · · · · · · · ·	

### PHOTOMETRIC CHARACTERISTICS

Color Rendering Index (CRI) (NOM)	83
Color Temperature (NOM)	2700 K
Initial Lumens (NOM)	750
Lumens per Watt (Efficacy) (NOM)	63 lm
Nominal Initial Lumens per Watt (NOM)	63

#### **ELECTRICAL CHARACTERISTICS**

Estimated Energy Cost per Year (NOM)	1.45
Voltage (NOM)	120.0
Wattage (NOM)	12.0

#### **DIMENSIONS**

Bulb Diameter (DIA) (NOM)	3.7500 in (95.2 mm)
Maximum Overall Length (MOL) (NOM)	5.3700 in (136.4 mm)

#### PRODUCT INFORMATION

Product Code	65389
Description	LED12DBR30/827

Standard Package	Case
Standard Package GTIN	10043168653890
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
UPC	043168653893

## **▲** CAUTIONS & WARNINGS