



Product Catalog

for professionals

[Products](#) > 65390

65390 – LED12DBR30/830

GE LED R30

This product is no longer manufactured.

- Energy-efficient LED lamps. Long life.



UL damp rated

GENERAL CHARACTERISTICS

Lamp type	Replacement Lamps - Directional
Bulb	BR30
Base	Medium Screw (E26)
ENERGY STAR® Qualified	Yes
Primary Application	Indoor Floodlight
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Finish	Frost
Bulb Shape	BR30
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	65 W
Lamp Type	LED-BR
Life in Years (NOM)	23 46
Rated Life (NOM)	50000 hrs

PHOTOMETRIC CHARACTERISTICS

Color Rendering Index (CRI) (NOM)	83
Color Temperature (NOM)	3000 K
Initial Lumens (Vert)	750
Initial Lumens (NOM)	750
Lumens per Watt (Efficacy) (NOM)	63 lm
Nominal Initial Lumens per Watt (NOM)	63

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year (NOM)	1.45
Voltage (NOM)	120.0
Wattage (NOM)	12.0

DIMENSIONS

Bulb Diameter (DIA) (NOM)	3.7500 in (95.2 mm)
Maximum Overall Length (MOL) (NOM)	5.3700 in (136.4 mm)

PRODUCT INFORMATION

Product Code	65390
--------------	-------

Description	LED12DBR30/830
Standard Package	Case
Standard Package GTIN	10043168653906
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	1
UPC	043168653909

 **CAUTIONS & WARNINGS**