



Product Catalog

for professionals

[Products](#) > 66129

66129 – LED7DMR16/830/35

GE LED MR16

This product is no longer manufactured.

- Energy-efficient LED lamps. Long life.



UL damp rated

GENERAL CHARACTERISTICS

Lamp type	Replacement Lamps - Directional
Bulb	MR16
Base	2-Pin (GU5.3)
ENERGY STAR® Qualified	Yes
Primary Application	Indoor Floodlight
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Shape	MR16
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	35 W
Lamp Type	LED-MR
Life in Years (NOM)	23
Rated Life (NOM)	25000 hrs

PHOTOMETRIC CHARACTERISTICS

Beam Spread (NOM)	35.0 °
Center Beam Candlepower (CBCP) (NOM)	1100
Color Rendering Index (CRI) (NOM)	84
Color Temperature (NOM)	3000 K
Initial Lumens (NOM)	390
Lumens per Watt (Efficacy) (NOM)	56 lm
Nominal Initial Lumens per Watt (NOM)	56

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year (NOM)	0.84
Voltage (NOM)	12.0
Wattage (NOM)	7.0

DIMENSIONS

Bulb Diameter (DIA) (NOM)	2.0000 in (50.8 mm)
Maximum Overall Length (MOL) (NOM)	1.8800 in (47.7 mm)

PRODUCT INFORMATION

Product Code	66129
Description	LED7DMR16/830/35
Standard Package	Case

Standard Package GTIN	10043168661291
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	1
UPC	043168661294

**CAUTIONS & WARNINGS**