

## Product Catalog for professionals

<u>Products</u> > 66132

## 66132 - LED7DMR16/827/35

GE LED MR16

This product is no longer manufactured. Remaining stock is on Firesale.

• Energy-efficient LED lamps. Long life.



UL damp rated

Lamp type	Replacement Lamps - Directional
Bulb	MR16
Base	2-Pin (GU5.3)
ENERGY STAR® Qualified	Yes
Primary Application	Indoor Floodlight
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Shape	MR16
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	35 W
Lamp Type	LED-MR
Life in Years (NOM)	23
Rated Life (NOM)	25000 hrs
PHOTOMETRIC CHARACTERISTICS  Beam Spread (NOM)  Center Beam Candlepower (CBCP)	35.0 ° 1100
(NOM)	
Color Rendering Index (CRI) (NOM)	84
Color Temperature (NOM)	2700 K
Initial Lumens (NOM)	370
Lumens per Watt (Efficacy) (NOM)	53 lm
Nominal Initial Lumens per Watt (NOM)	53
ELECTRICAL CHARACTERISTICS	
Estimated Energy Cost per Year (NOM)	0.84
Voltage (NOM)	12.0
Wattage (NOM)	7.0
DIMENSIONS	
Bulb Diameter (DIA) (NOM)	2.0000 in (50.8 mm)
Maximum Overall Length (MOL) (NOM)	1.8800 in (47.7 mm)
PRODUCT INFORMATION	
Product Code	66132
Description	LED7DMR16/827/35
Standard Package	Case
otaliaala i dollago	

Standard Package GTIN	10043168661321
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	1
UPC	043168661324

## **▲** CAUTIONS & WARNINGS