

Product Catalog for professionals

<u>Products</u> > 65138

65138 - LED12DP30S827/35

GE LED PAR30

This product is no longer manufactured.

• Energy-efficient LED lamps. Long life.



UL damp rated

FNFR			

Lamp type	Replacement Lamps - Directional
Bulb	PAR30
Base	Medium Screw (E26)
ENERGY STAR® Qualified	Yes
Primary Application	Indoor Floodlight
Additional Info	GE Life Rating is based on 70% Lumen Maintenance
Bulb Shape	PAR30
Color	Silver
Dimming Capability	Operates on dimming circuits. See GELighting.com/dimming for further information
Equivalent Wattage (NOM)	90 W
Lamp Type	LED-PAR
Life in Years (NOM)	23
Rated Life (NOM)	25000 hrs

PHOTOMETRIC CHARACTERISTICS

Beam Spread (NOM)	35.0 °
Center Beam Candlepower (CBCP) (NOM)	2000
Color Rendering Index (CRI) (NOM)	83
Color Temperature (NOM)	2700 K
Initial Lumens (NOM)	740
Lumens per Watt (Efficacy) (NOM)	62 lm
Nominal Initial Lumens per Watt (NOM)	62

ELECTRICAL CHARACTERISTICS

Estimated Energy Cost per Year (NOM)	1.45
Voltage (NOM)	120.0
Wattage (NOM)	12.0

DIMENSIONS

Bulb Diameter (DIA) (NOM)	3.7500 in (95.2 mm)
Maximum Overall Length (MOL) (NOM)	3.7500 in (95.2 mm)

PRODUCT INFORMATION

Product Code	65138
Description	LED12DP30S827/35
Standard Package	Case

Standard Package GTIN	10043168651384
Standard Package Quantity	6
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	1
UPC	043168651387

▲ CAUTIONS & WARNINGS