



Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
12 V DC	No
24 V DC	Yes
Analog outputs	
Number of analog outputs	2
Output ranges, voltage	
• 0 to 10 V	Yes
EMC	

Emission of radio interference acc. to EN 55 011	
• Emission of radio interference acc. to EN 55 011 (limit class B)	Yes
Degree and class of protection	
IP20	Yes
Standards, approvals, certificates	
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
acc. to VDE 0631	Yes
Marine approval	
• Marine approval	Yes
Ambient conditions	
Operating temperature	
• min.	0 °C
• max.	55 °C
Dimensions	
Width	35.5 mm
Height	90 mm
Depth	58 mm
<b>last modified:</b>	21.08.2014