



Board to wire interface

Shrouded pin header 5.08 mm (.200) pitch.

- 6340 series are male headers designed to receive crimp female plugs of series 6310 or IDC female plugs of series 6320.
- Provided with a locking and polarization device ensuring fail safe resistance and avoiding any contact mismatch. Stands-off allow cleaning after soldering.
- Available in one row with 2 to 10 contacts.

Special features

- Insulator : self extinguishing thermoplastic (UL 94 VO). Flow solder resistant.
- Contact : square pin (1.14mm²). Material : copper alloy.

How to order

Series prefix	6340	06	1	D1	3	00
Number of contacts per row	02 to 10					
Number of rows	1					
Contact type	D1 : straight C1 : right angle					
Contact plating	2 : gold flash 3 : tinned					
Option :	00 : B = 3.7 for 2.4 mm PCB					

