



Timers

T&B Catalog Number:

1SVR730030R3300

UPC Number:

80432558375

Status:

Active

Description:

Timer with adjustable time delays from 0.05 sec. to 300 hrs. in 2 x 10 ranges, and 24-48 VDC or 24-240 VAC rated control supply voltage, control input with voltage-related triggering, and 2 SPDT (c/o) output contacts

Features

Selectable timing functions: Impulse ON-OFF, ON-OFF Delay, Single Pulse Generator, ON Delay (accumulative) , Fixed Impulse with Time Delay, Recycling, ON-OFF No Delay

Has connections for 2 potentiometers

Application

For use in applications where the timing function must be selected for the application

For applications where external adjustment is required

General

Series	CT-S
Output Contacts	2 SPDT
Operation-Function	Multifunction Timer

Dimension Information

L x W x D (inches)	3.07 x 0.87 x 4.08
--------------------	--------------------

Specifications

Supply Voltage (AC)	24-240
Supply Voltage (DC)	24-48
LED Indicator	3
Time Delay	0.05 sec - 300 hrs. in 2 x 10 ranges

Packaging

Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	0.38 lbs. Each

Certifications

Approvals	UL
-----------	----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com