


## **IEC Square Distribution Units**


## PXD701/061/10/1

- Six Shuttered Outlets
- 5 x 20mm Fuseholder
- Filtered or Non Filtered
- Switch, Fuse, Neon Indicator
- With IEC Inlet
- 10A, 250V a.c.






- Six Shuttered Outlets
- 5 x 20mm Fuseholder
- Switch, Fuse, Neon Indicator
- Screw Fit to Panel
- 10A, 250V





- Six Shuttered Outlets
- 5 x 20mm Fuseholder
- Filtered or Non Filtered
- Switch, Fuse, Neon Indicator
- 2 Metre Cable with BS1363 or CEE7 Plug
- 10A, 250V



Specification	1	Part No.	Inlet	Outlet	EMI Filter	Switch	Fuse	Neon Indicator
Mouldings:	Thermoplastic	Panel Style:						
Housing:	ABS	PXD500/061/10/1		6 Shuttered		1	1	1
Connectors:	Nylon	Box Style:						
Contacts:	Outlets: Brass, Tin Plated Inlets: Brass, Nickel Plated	PXD701/061/10/1	1	6 Shuttered		1	1	1
		PXD701/561/10/1	1	6 Shuttered	1	1	1	1
Voltage Rating:	250V a.c. 50/60Hz	PXD703/061/10/1	2m cable	6 Shuttered		1	1	1
Current Rating:	10A		with BS 1363 plug					
Proof Voltage:	2kV	PXD703/561/10/1	2m cable	6 Shuttered	1	1	1	1
Temp. Range:	-5°C to +60°C		with					
RoHS	Compliant	PXD706/061/10/1	BS 1363 plug  2m cable  with CEE7	6 Shuttered		1	1	1
Filter		_	Sheet VII plug					

Max. Earth Leakage:

Current:

<0.35mA (at 250V, 50Hz)

**Capacitor**: 2 x 2.2nF (Y), 1 x 15nF (X)

Inductance: 2 x 0.35mH

Fuse: 5 x 20mm, 10A (ceramic HRC type, IEC 127)

Other configurations available on request.

www.elektron-bulgin.com