

NEW

Legrand cabling system LCS²

category 6

RJ 45 sockets



673 45 + cover plate titanium 685 51



778 91



695 69

Pack	Cat.Nos	Arteur RJ 45 socket cat. 6
10	5723 02	UTP - 1 module <ul style="list-style-type: none"> ○ White ● Magnesium
10	5728 02	
10	5723 14	UTP - 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium
10	5728 14	
10	5723 24	UTP - 2 modules - round <ul style="list-style-type: none"> ○ White ● Magnesium
10	5728 24	
5	5723 53	UTP with controlled access - 2 modules Supplied with 2 keys for 5 sockets <ul style="list-style-type: none"> ○ White with red shutter ● Magnesium with red shutter
5	5728 53	
1	5723 39	UTP retractable RJ 45 sockets - 4 modules With integrated retractable cord (0.9 m) Winds up automatically with a pushbutton <ul style="list-style-type: none"> ○ White ● Magnesium
1	5728 39	
10	5723 22	FTP - 1 module <ul style="list-style-type: none"> ○ White ● Magnesium ○ White with orange shutter ● Magnesium with orange shutter ○ White with green shutter ● Magnesium with green shutter
10	5728 22	
10	5723 54	
10	5728 54	
10	5723 55	
10	5728 55	
10	5723 16	FTP - 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium
10	5728 16	
10	5723 23	Shielded STP - 1 module <ul style="list-style-type: none"> ○ White ● Magnesium
10	5728 23	
10	5723 17	Shielded STP - 2 modules <ul style="list-style-type: none"> ○ White ● Magnesium
10	5728 17	

Pack	Cat.Nos	Celiane RJ 45 sockets cat. 6
		UTP socket To create a 1-gang socket, combine mechanism Cat.No 673 44 and a cover plate Cat.No 682 51 (white) or Cat.No 685 51 (titanium) To create a 2-gang socket, combine 2 mechanisms Cat.No 673 46 and a cover plate Cat.No 682 52 (white) or Cat.No 685 52 (titanium)
10	673 44	UTP socket
		UTP retractable RJ 45 socket - 4 modules With integrated retractable cord (0.9 m) Winds up automatically with a pushbutton
10	673 54	To create a 1-gang socket, combine mechanism Cat.No 673 54 and a cover plate Cat.No 682 55 (white) or Cat.No 685 55 (titane)
		FTP socket To create a 1-gang socket, combine mechanism Cat.No 673 45 and a cover plate Cat.No 682 51 (white) or Cat.No 685 51 (titanium). To create a 2-gang socket, combine 2 mechanisms Cat.Nos 673 46 and a cover plate Cat.No 682 52 (white) or Cat.No 685 52 (titanium)
10	673 45	FTP socket
		FTP retractable RJ 45 socket - 4 modules With integrated retractable cord (0.9 m) Winds up automatically with a pushbutton
10	673 55	To create a 1-gang socket, combine mechanism Cat.No 673 55 and a cover plate Cat.No 682 55 (white) or Cat.No 685 55 (titane)
		STP socket To create a 1-gang socket, combine mechanism Cat.No 673 96 and a cover plate Cat.No 682 51 (white) or Cat.No 685 51 (titanium). To create a 2-gang socket, combine 2 mechanisms Cat.No 673 46 and a cover plate Cat.No 682 52 (white) or Cat.No 685 52 (titanium)
10	673 96	STP socket
10	331 81	Keystone RJ 45 sockets cat. 6 UTP socket connected with 110 tool
10	778 91	Soliroc RJ 45 sockets cat. 6 - IK 10 IP 20 For at-risk areas or areas with no surveillance FTP socket
5/100	695 69	Plexo RJ 45 sockets cat. 6 - IP 55 closed flap IK 07 Protection against water, dust For industrial sites
1/20	695 61	
1	695 81	
		FTP socket <ul style="list-style-type: none"> ○ Grey/white ● UTP socket ○ Grey/white ● Adapter for RJ 45 socket ● Weatherproofing ensured (IP 44) ● plug inserted ○ Grey/white

Mosaic and Arteur sockets with copper feedthrough (p. 63)

Mosaic and Arteur audio/video sockets (p. 80)