



Actual



Representative

Catalog Number: GUAL14-TB
Product ID: 7TAD013360R0024
UPC Number: 78621034451
Status: Active

1/2 Inch GUAL Hazardous Location Conduit Outlet Box, Box Ductile Iron Zinc Plated, Cover Die Cast Aluminum, 7.1 Cubic Inch

- All boxes are furnished with internal grounding screw.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Brand Name	T&B
Type	GUA Conduit Outlet Boxes & Covers-Explosionproof
Special Features	All Hubs Have a Minimum of Five Full Threads and Integral Bushing
Application	GUA Boxes Can Be Used for Hazardous Location Conduit Runs for The Following: (1) Allows for Mounting of Fixutre Outlets When Used with Appropriate Covers; (2) Provides Easy Access to Wiring; (3) Provides Junction In Conduit for Wire Pulling and Splices; (4) Changes Direction In Rigid Conduit Systems; (5) Attaches Two or More Pieces of Conduit Long Runs; (6) Guards Against Damage to Wires In Rigid Conduit.
Standard	UL E202368, CSA
Hub Size	1/2 Inch
Material	Ductile Iron
Finish	Zinc Plated

Packaging

Outer Quantity	1
Outer Dimensions (inches)	5.5x5.5x3.62
Weight Uom	171 lbs. per 100

Documents / Support Tools

Technical Data Sheet US Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email:techsupport@tnb.com