




Actual



Representative

**Catalog Number:** EYS61-TB  
**Product ID:** 7TAD013390R0007  
**UPC Number:** 78621024811  
**EAN Number:** 05415022264906  
**Status:** Active

2 Inch EYS Sealing Fitting, Body Ductile Iron, Plug Gray Iron, Nipple Steel

- All hubs have a minimum of five full threads, integral bushings to protect conductor insulation from damage, and large access openings for easier packing of sealing material.
- Seals are approved to be used with Crouse Hinds & #174; Sealing Compound and Fiber.

### Header

3D Model Available on Website

### North American Specifications (UNSPSC)

UNSPSC	39131708 Electrical conduit fitting body
IGCC	5563 Electrical conduit fitting body
Brand Name	T&B
Type	Sealing Fitting - Vertical/Horizontal
Special Features	Minimum of Five Full Threads and Integral Bushing
Application	Seals Sections of Conduit Runs from Passage of Vapors, Flame, and Gases
Standard	UL E193396, CSA
Hub Size	2 Inch
Length	6-1/4 Inch
Material	Iron
Finish	Zinc-Plated with Aluminum Acrylic Paint

### Packaging

Outer Quantity	1
Outer Dimensions (inches)	5x3.5x9
Weight Uom	6.26 lbs. Each

### Documents / Support Tools

Technical Data Sheet US Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)