


NOTES:

1. TERMINATION PROGRAMMABLE VIA SLIDE SWITCH:  
ON: TERMINATED  
OFF: PASSIVE TEE
2. SUPPORTS TRANSMISSION RATES UP TO 12 Mbits/sec.
3. FIELD WIREABLE 9 PINS, D-SUB FOR PROFIBUS COMMUNICATION.



SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION 	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		<b>TURCK INC</b> High Technology Sensors and Automation Controls 3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
	MATERIAL	DRFT RWC	DATE 03/24/08	DESCRIPTION CONNECTOR,PDP,D9SM	
FINISH	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY	DSGN	SCALE 1=1.0	IDENTIFICATION NO. A9426	
	CONTACT TURCK FOR MORE INFORMATION	UNIT OF MEASUREMENT <b>MILLIMETER [ INCH ]</b>		REV C	
C	GET CONNECTOR LABELS TO SHOW	RDS	12/14/09	29165	
REV	DESCRIPTION	BY	DATE	ECO NO.	DO NOT SCALE THIS DRAWING
					FILE: A9426
					SHEET 1 OF 1