

18-013, 5PG

Air Pressure Gauges
1/8" and 1/4" Port Sizes

Center Back Connection

Outer Scale Scale psig	Scale Range Middle Scale bar	Inner Scale Mpa	1/8 NPT 1.5" (40mm) Diameter	1/8 NPT 2" (50mm) Diameter	1/4 NPT 2" (50mm) Diameter
0 to 30	0 to 2	0 to 0.2	18-013-214	18-013-201	18-013-207
0 to 60	0 to 4	0 to 0.4	18-013-211	18-013-202	18-013-208
0 to 100	0 to 7	0 to 0.7	—	18-013-203	18-013-235
0 to 160	0 to 11	0 to 1.1	18-013-212	18-013-204	18-013-209
0 to 300	0 to 20	0 to 2.1	—	18-013-205	18-013-210
0 to 400	0 to 28	0 to 2.8	—	18-013-206	—

Bottom Connection

2" (50 mm) diameter gauges do not have the Mpa scale

Outer Scale Range-psi	Middle Scale Range-bar	Inner Scale Range-Mpa	1/8 NPT 1.5" (40mm) Dia.	1/4 NPT 2" (50mm) Dia.
0 to 15	0 to 1	—	—	18-013-082
0 to 30	0 to 2	0 to 0.2	18-013-224	18-013-030 *
0 to 60	0 to 4	0 to 0.4	18-013-225	18-013-083 *
0 to 100	0 to 7	0 to 0.7	18-013-265	18-013-084 *
0 to 160	0 to 11	0 to 1.1	18-013-273	18-013-085 *
0 to 300	0 to 20	—	—	18-013-086 *
0 to 2000	0 to 135	—	—	18-013-244 *†
0 to 3000	0 to 205	—	—	18-013-087 *†

* Underwriters Laboratories Inc. Listed
† Shipped with pulsation dampener installed.

Center Back Connection, Panel Mount

Outer Scale Range-psi	Middle Scale Range-bar	Inner Scale Range-Mpa	1/8 NPT Male and 10-32 Female 1.5" (40mm) Diameter
0 to 30	0 to 2	0 to 0.2	5PG-306-000 **
0 to 60	0 to 4	0 to 0.4	5PG-312-000 **
0 to 100	0 to 7	0 to 0.7	5PG-320-000 **

Center Back Connection

Outer Scale Range-bar	Middle Scale Range-Mpa	Inner Scale Range-psi	R1/8 1.5" (40mm) Diameter	R1/8 2" (50mm) Diameter
0 to 1.6	0 to 0.16	0 to 23	18-013-991	18-013-010
0 to 4	0 to 0.4	0 to 56	18-013-990	18-013-011
0 to 6	0 to 0.6	0 to 84	—	18-013-012
0 to 10	0 to 1.0	0 to 140	18-013-989	18-013-013
0 to 16	0 to 1.6	0 to 240	—	—
0 to 25	0 to 2.5	0 to 360	—	18-013-014

Blow Guns BG Series

1/4" Port Size

Port (PTF)	Part Number	Description
1/4"	BG4200	Metal blow gun
1/4"	BG3200	Plastic blow gun
1/8"	BG0200	Rubber Tip**

** Units are not O.S.H.A. compliant without air exhaust mechanism.
Air exhaust mechanism must be removed to use the rubber tip.

Triple calibrated scale indicates pressure in psi, bar, and Mpa (megapascal)

Back or bottom connection

Panel mount, stainless steel, and Underwriters Laboratories, Inc. listed gauges available



Stainless Steel Gauges

Gauges do not have the Mpa scale

Outer Scale Range-bar	Inner Scale Range-psi	1/8 PTF 1.5" (40mm) Dia	1/4 PTF 1.5" (40mm) Dia.
0 to 6	0 to 84	—	18-013-913
0 to 10	0 to 140	18-013-844	18-013-909
0 to 25	0 to 360	—	18-013-905
0 to 160	0 to 11	—	18-013-917

OSHA compliant**

Exhausts air when nozzle is blocked

