


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|---|---------|-------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | - | - |
| B | ECN 4580:REVISED DRAWING AND NEW FORMAT | 2/25/10 | D.FRISIELLO |
| | | | |
| | | | |



| DESCRIPTION | MATERIAL | FINISH |
|----------------|-----------------|--------------|
| BODY | BRASS | NICKEL PLATE |
| PIN | BRASS | GOLD PLATE |
| DIELECTRIC | PTFE | - |
| GROUND RING | BRASS | NICKEL PLATE |
| RETAINING RING | BRASS | NICKEL PLATE |
| GASKET | SILICONE RUBBER | ORANGE |
| SHELL | BRASS | NICKEL PLATE |
| RESISTOR | - | - |



NOTES:

ELECTRICAL:
 IMPEDANCE: 50 OHM
 FREQUENCY RANGE: 0 - 6 GHz
 VSWR: 1.5 : 1 MAX.
 POWER RATING: 1 WATT

RoHS Compliant ✓

| | | | | | |
|---|----------------------------|------------------|--|-----------------------|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] DIMENSIONAL TOLERANCES: .X = ±.1 .XX = ±.01 .XXX = ±.005 ANGULAR TOLERANCES: ALL = ± 1° | APPROVALS | DATE |  45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | | |
| | DRAWN BY D.FRISIELLO | 2/25/10 | | | |
| | CHECKED BY K.BURGNER | 2/25/10 | CATEGORY COAXIAL | | |
| | APPROVED BY K.BURGNER | 2/25/10 | PRODUCT DESCRIPTION N MALE 50 OHM, TERMINATOR | | |
| PROJECTION  | COLOR VARIATIONS MAY OCCUR | SIZE A | FSCM NO. 43321 | DWG. NO. ANM-TERM1 | REV. B |
| | | SCALE: NONE | CAD FILE: ANM-TERM1.SLDDRW | SHEET 1 OF 1 | |