

**Manual Transfer Switch**
T&B Catalog Number:

OT400U30C

UPC Number:

66201921378

Status:

Active

Description:

3 pole, 400 amps rated at 600 VAC, UL 98, double throw open non-fusible disconnect switch

Features

Quick make, quick brake mechanism

Extremely compact size

Finger-proof construction with no hazardous exposed parts

Application

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.

Motor feeder applications and motor feeder short circuit and ground fault protection

Kits with base and/or DIN rail mounted switches and pistol handles

General

Style Double Throw

Number of Poles 3

Series Non-fusible

Approvals

UL Class UL 98

Dimension Information

H x W x D (inches) 7.28 x 9.88 x 7.97

Specifications

Rated Current (Amps) 400

Rated Voltage AC 600

Packaging

Package in Units 1

T&B Sold in UOM Each

T&B Weight Per UOM 14.02 lbs. Each

For further technical assistance, please contact us...Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.comT&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com