



Mounting hole (inch)	0.7480"
Mounting hole (metric)	19mm
Indicator type	standard
Mounting type	with bezel
Bezel type	prominent
Bezel material	metal
Bezel color	satin chrome
Bezel size	M19
Protection	IP67
Lens type	flat
Lens color	blue diffused
Lens size	10mm
Connector Tpe	tab terminals 2.8x0.8
Connector number	2
Connector for lamp test	no
Number LED chip	1
Indicator color	blue
Dom wave length	470nm
Peak Wave Lenght (mA)	
Op. voltage (V)	12V AC/DC

Drawn : ROJ	Ch'd : ROJ	Datasheet : 1971	Print date : 18/07/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :



Part Number : 19710257
 Serial Number : 1971
 LEDs Indicators

Forward volt max.	
Rectifier	Half Wave
AC current	7mA
DC current	14mA
Lum in min (mcd)	
Lum in type (DC)	350mccd
Voltage tolerance (%)	10%
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	
Viewing angle (°)	
ROHS Status	Yes

Drawn : ROJ	Ch'd : ROJ	Datasheet : 1971	Print date : 18/07/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :