



Based LED type	MultiLED
Size (inch)	T5.5k
Size (mm)	T5.5k
Housing size	5.7x22mm
Base	T5.5k
Chip number	4
Chip color	red
Wavelength (nm)	620
Op. voltage (V)	28
Rectifier	Protection Diode
AC current	-
DC current	16
Type I_v DC current	26
Voltage tolerance (%)	10%
Op. temperature (°C)	-20°C...+60°C
Storage temperature (°C)	-25°C...+80°C
ROHS Status	Yes

Drawn : DIL	Ch'd : DIL	Datasheet : 15040	Print date : 06/09/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :