



Mounting hole (inch)	0.8661"
Mounting hole (metric)	22mm
Indicator type	standard
Mounting type	with bezel
Bezel type	prominent
Bezel material	metal
Bezel color	black chrome
Bezel size	M22
Protection	IP67
Lens type	flat
Lens color	green diffused
Lens size	16mm
Connector Tpe	tab terminals 2.8x0.8

Drawn : ROJ	Ch'd : ROJ	Datasheet : 195F	Print date : 11/07/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :



Part Number : 195F1131M
 Serial Number : 195F
 LEDs Indicators

Connector number	3
Connector for lamp test	no
Number LED chip	1
Indicator color	green
Dom wave length	525nm
Peak Wave Lenght (mA)	
Op. voltage (V)	130V AC
Forward volt max.	
Rectifier	Half Wave
AC current	6mA
DC current	-
Lum in min (mcd)	
Lum in type (DC)	150mcd
Voltage tolerance (%)	10%
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	with protection tube
Viewing angle (°)	
ROHS Status	Yes

Drawn : ROJ	Ch'd : ROJ	Datasheet : 195F	Print date : 11/07/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :