



Based LED type	MultiLED
Size (inch)	T-1 3/4
Size (mm)	T6
Housing size	6.1x15.9mm
Base	MG
Chip number	6
Chip color	red
Wavelength (nm)	620
Op. voltage (V)	24
Rectifier	Protection Diode
AC current	-
DC current	14
Type Iv DC current	34
Voltage tolerance (%)	10%
Op. temperature (°C)	-20°C...+60°C
Storage temperature (°C)	-25°C...+80°C
ROHS Status	Yes

Drawn : DIL	Ch'd : DIL	Datasheet : 15121M	Print date : 25/07/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :