



Mounting hole (inch)	0.3150"
Mounting hole (metric)	8mm
Indicator type	standard
Mounting type	with bezel
Bezel type	prominent
Bezel material	metal
Bezel color	black chrome
Bezel size	M8
Protection	IP40
Lens type	round
Lens color	yellow diffused
Lens size	5mm
Connector Tpe	tab terminals 2.8x0.8mm
Connector number	2
Connector for lamp test	no
Number LED chip	1
Indicator color	yellow
Dom wave length	588nm
Peak Wave Lenght (mA)	
Op. voltage (V)	12V DC
Forward volt max.	
Rectifier	-
AC current	-
DC current	20mA
Lum in min (mcd)	

Drawn : ROJ	Ch'd : ROJ	Datasheet : 1904	Print date : 12/09/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :



Part Number : 19041252
Serial Number : 1904
LEDs Indicators

Lum in type (DC)	32mcd
Voltage tolerance (%)	10%
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	
Viewing angle (°)	
ROHS Status	Yes

Drawn : ROJ	Ch'd : ROJ	Datasheet : 1904	Print date : 12/09/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :