

Product Datasheet

[Catalog Home](#)[Home Page](#)[Search](#)

SHC1034ZP -- Cord Connectors

Machined
Zinc-Plated Steel

The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and other corrosive materials.

Product Specifications

Product Type	Cord Connectors
Material/Style	Zinc Plated Steel
Cord Diameter Range	.50"- .63" (12.7- 15.9)
Cord Connector Body Style	Straight Male
Form Size	F2
HUB Size	3/4"
Color Code	Brown
Effective Operating Temperature	-30°F to +225°F (-34°C to +107°C)
Recommended Knockout Hole Size	1.09"- 1.14" (27.8-29.0)
Flammability	Hubbell nylon cord connectors have a UL 94-V2 rating.
Hazardous Locations	Hubbell cord connectors are suitable for use in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 N.E.C. Reference 501-4(b), 502-4(a), 502-4(b), 503-3(a), and 503-3(b).
Dimension A A/C	1.27" (32.3)
Dimension A A/F	1.13" (28.7)
Dimension B	1.20" (30.5) Ref.
Dimension C	.55" (14.0)
Dimension D	.64" (16.3) Throat Dia.
Dimension E A/C	1.29" (32.8)
Dimension E A/F	1.13" (28.7)
Certifications	UL Listed in accordance with Standard 514B, CSA Certified, United States Coast Guard Approval, Title 46-Part 111.
UPC Number	78358549620
Weight in LBs	0.275
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog



