



Based LED type	MultiLED
Size (inch)	T6.8
Size (mm)	T6.8
Housing size	6.8x46.5mm
Base	T6.8
Chip number	6
Chip color	yellow
Wavelength (nm)	585
Op. voltage (V)	24
Rectifier	Protection Diode
AC current	-
DC current	15
Type Iv DC current	63
Voltage tolerance (%)	10%
Op. temperature (°C)	-20°C...+60°C
Storage temperature (°C)	-25°C...+80°C
ROHS Status	Yes

Drawn : DIL	Ch'd : DIL	Datasheet : 15071	Print date : 11/07/06
Revision :	Revision date : 2006-03-06	Name : DIL	Scale :