



## 2127934-6 Product Details

[Share](#) [Print](#) [Email](#)



**2127934-6**

TE Internal Number: 2127934-6

Active

### Cable Assemblies

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- High Speed Cable Assembly Category, Industry Standard Cable Assembly Category, Small Form Factor Pluggable (SFP) Cable Assembly Category
- Cable Assembly Type = Pluggable / Direct Attach
- SFP+ Cable Assembly Sub-Type
- 10 Gigabit Ethernet Application, Fibre Channel Application, Infiniband compliant Application
- Assembly Type = SFP+ 10Gbps Passive

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

### Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Cable Assembly Category = High Speed, Industry Standard, Small Form Factor Pluggable (SFP)
- Cable Assembly Type = Pluggable / Direct Attach
- Cable Assembly Sub-Type = SFP+
- Assembly Type = SFP+ 10Gbps Passive
- Color = Black
- Keyed = No
- Cable Style = Madison TurboTwin
- Latching Style = Retractable Pin

#### Electrical Characteristics:

- Data Rate (Gb/s) = 10

#### Dimensions:

- Length (M [ft]) = 5.00 [16.40]

#### Body Features:

- Equalized = No
- Release Type = Pull Tab Release
- Strain Relief Type = Overmold

#### Configuration Features:

- Configuration = Double Ended
- Number of Positions = 2 Pair
- Number of Signal Positions = 4
- Number of Power Positions = 0
- Shielded = Yes

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Conditions for Usage:

- Wire Size - Details = 24 AWG

#### Operation/Application:

- Application = 10 Gigabit Ethernet, Fibre Channel, Infiniband compliant

#### Product Availability:

- Region = Not Specified

#### Other:

- Brand = TE Connectivity

Feedback

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed



