

## QUICK DISCONNECTS



✓ Active



### TE CONNECTIVITY (TE)

110 FF RCPT 22-20 010TPBR FASTIN-FASTON | FASTON Terminals and Housings

160308-2 TE Internal Number: 160308-2

#### Always EU RoHS/ELV Compliant

Mating Tab Width 2.79 mm [.11 in] Mating Tab Thickness .79 mm [.031 in] Wire Insulation Diameter 1.3 – 2 mm [.051 – .078 in] Wire Size (AWG) 22 – 20 Wire Size (mm<sup>2</sup>) .3 – .6

LOOSE PIECE .110 SER FASTON RECEPTACLE

Product Drawings

CAD Files

3D PDF PDF 3D

PDF **English** 

Customer View Model 2D\_DXF.ZIP English

Customer View Model 3D\_IGS.ZIP English

Customer View Model 3D\_STP.ZIP English

Please review product documents or **contact us** for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Wire Stop	No
	Disconnect Type	Quick Disconnect
	Insertion Force	Normal
	FASTON	Yes
	Wire/Cable Type	Regular Wire
	Insulated Wire Support	Yes
	Support Style	Insulation Support
	Applies To	Wire/Cable

#### Ƴ 🖬 f 🔻

Configuration Features	Terminal Angle Connection Capacity	Straight Single
Body Features	Plating Material	Brass, Tin
Contact Features	Terminal Orientation	Straight
Termination Features	Crimp Type	F-Crimp
Mechanical Attachment	Mating Retention Type	Locking Lance
Dimensions	Mating Tab Width	2.79 mm [ .11 in ]
	Mating Tab Thickness	.79 mm [ .031 in ]
	Wire Insulation Diameter	1.3 – 2 mm [ .051 – .078 in ]
	Wire Size (AWG)	22 – 20
	Wire Size (mm²)	.3 – .6
	Material Thickness	.25 mm [ .01 in ]
	Overall Length	15.24 mm [ .6 in ]
Operation/Application	For Housing Type	Single or Multiple
Packaging Features	Packaging Method	Bag
	Packaging Quantity	1000
Other	Comment	According to DIN 46340, Part 1
Product Compliance	Statement of Compliance PDF	

VIEW ALL PRODUCT COMPLIANCE

# CUSTOMERS ALSO BOUGHT



