

Molded Case Circuit Breakers T&B Catalog Number:

T2S050MW

UPC Number: 66201906770

Status: Active

Description:

3 pole, 50 amps rated at 240-480V AC, Tmax molded case circuit breaker with magnetic only (MCP) trip device and 35kA at 480V AC interrupt current rating

Features	
	Short circuit protection is provided by an adjustable instantaneous only, magnetic trip unit (MCP)
	Advanced contact design and arcing chambers provide the latest in fault current protection
	Adjustable trip point from 300 to 600A
	Advanced contact design and arcing chambers provide the lastest in fault current protection
Application	
	For motor control applications (MCP)
	Can be installed in either the horizontal or vertical planes
	Suitable for reverse feed applications
General	
Trip Type	Magnetic only (MCP)
Number of Poles	3
Series	T2
Approvals	
UL Class	UL 489
Dimension Information	
H x W x D (inches)	5.12 x 3.54 x 2.76
Specifications	
Rated Current (Amps)	50
Rated Voltage AC	240 - 480
Interrupt Rating	35kA at 480V AC
Packaging	
Package in Units	1
T&B Sold in UOM	Each
T&B Weight Per UOM	2.74 lbs. Each
Certifications	



File Nbr: UL 489

For further technical assistance, please contact us...

T&B Technical Support MS 3B-50 8155 T&B Blvd. Memphis, TN 38125 Hours: 7AM - 6PM CDT Monday-Friday Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com