

Office

JD-0700EU-2



Actual product may vary from the image shown

Professional Wireless Desktop for Entry Level Users!

The compact and high-quality JD-0700EU-2 desktop set from CHERRY, features an excellent price/performance ratio, modern, flat design with gentle, quiet and durable wear-resistant keys.

Facts & Features

- Whisper quiet keystroke keys with wear-resistant laser key legends
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- Symmetrical design: 3-Button mouse, suitable for both left-handed and right-handed operation
- Optical Sensor technology: 1200 dpi
- Rapid installation: Simple plug and play
- Interference-free wireless connection: Maximum wireless range (up to 8 meters) using 2.4 GHz wireless technology
- Nano USB receiver

Technical Data

Housing and Key Color:

Black

Weight (product):

Approx. 502 g/1.10 lbs (keyboard with battery), approx. 85 g/ .18 lbs (mouse with battery), approx. 1.5 g/ .003 lbs (receiver)

Total Weight (with packaging):

Approx. 923 g/ 2.0 lbs

Technical Data Cont.

Transmission Range :

10m / 32.80'

Frequency range:

2.400 GHz - 2.4835 GHz

Storage Temperature:

-20°C to 65°C / -4°F to 149°F

Operating Temperature:

0° C - 50° C / 32° F - 122° F

Current Consumption:

Typ. 3 mA (keyboard), Typ. 6 mA (mouse), max. 35 mA (receiver)

Interface:

USB

Product approvals:

UL 

c-tick 

CE 

FCC 

TÜV/GS 

System Requirements:

USB connection

Delivery Volume:

- 1 battery (type AA)
- 1 nano USB transmission receiver
- Operating instructions in hard copy
- 1 battery (type AAA)
- 1 optical wireless mouse
- 1 wireless keyboard

Dimensions (product):

458 x 170 x 20 mm / 18.03" x 6.69" x .78" (keyboard), 109 x 62 x 37mm / 4.2" x 2.4" x 1.4" (mouse), 18 x 13 x 5 mm / .70" x .51" x .19" (receiver)



Technical Data Cont.

Packaging Dimensions:

Approx. 549 x 200 x 45 mm /
23.6" x 8.2" x 2"

Reliability:

- MTBF > 45,000 hours

Mouse:

- Scanning: Infrared
- Resolution: 1200 dpi
- Number of Keys: 3
- Mouse Wheel Design: Scroll Wheel with Key Function
- Design: Symmetrical
- Connection: Wireless
- Scanning Rate: Max. 2400/s
- Housing Color: Black
- Key Color: Black

Keyboard:

- Key Technology: LPK
- Service Life, Standard Key: > 10 million Key Operations
- Inscription Layout: Standard
- Number of Keys: 104 + 4

Packaging Unit:

Number of products in the master package: 6
Number of master packages per pallet: 21

Warranty:

2 years

Order Description

<i>Order Number</i>	<i>Color</i>	<i>Number of Keys</i>
JD-0700EU-2	Black	104+4 Keys

ZF Electronic Systems Pleasant Prairie, LLC
11200 88th Avenue
Pleasant Prairie, WI 53158
USA
Phone: 262.942.6500
Internet: www.cherrycorp.com

Sales: 262.942.6500
E-Mail: cep_sales@ZF.com
Fax: 262.942.6566

The manufacturer accepts no liability for errors or non-availability, and reserves the right to change specifications without prior notice. Technical data relates to product specifications only. Features may differ from those described. Only drawings combined with product specifications shall be deemed binding.

© 2013 ZF Electronic Systems Pleasant Prairie, LLC
Last update: August 6, 2014