

Share:



APCRBC135



Description: Genuine APC RBC(TM) are tested and certified for compatibility to restore UPS performance to the original specifications.

Includes : Installation guide

[Product Overview](#)

[Technical Specifications](#)

[Documentation](#)

[Options](#)

Output

[Print Technical Specification](#)

Battery Output Voltage 24

Batteries & Runtime

Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Stand alone battery stack
Battery Placement	Internal Battery
Expected Battery Life (years)	3 - 5
RBC Quantity	1
Battery blocks per string	2

Physical

Maximum Height	107mm , 10.7CM
Maximum Width	107mm , 10.7CM
Maximum Depth	144mm , 14.4CM
Net Weight	4.68KG
Shipping weight	5.14KG
Shipping Height	229mm , 22.9CM
Shipping Width	229mm , 22.9CM
Shipping Depth	229mm , 22.9CM
Units per Pallet	100.0

Environmental

Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000meters

Conformance

Standard warranty 1 year repair or replace

Sustainable Offer Status

RoHS

Compliant

REACH

REACH: Contains No SVHCs