

Rittal – The System.

Faster – better – everywhere.

► Ex Enclosures Plastic, empty enclosure with hinged door – KE 9205.600

Date : Mar 19, 2018

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Ex Enclosures Plastic, empty enclosure with hinged door – KE 9205.600

created: 19.03.2018 build on www.rittal.com/us-en



Product description

Applications: Zone 1 and 2 or 21 and 22 to 94/9/EC
Ambient temperature range: -30°C...+80°C
The specified temperatures can be limited by the installed equipment
Protection type to EN 60 079: Equipment protection due to increased safety, equipment protection due to enclosure

Material: Housing: fiber-glass reinforced unsaturated polyester, surface resistance: $< 10^9 \Omega$
Door: fiber-glass-reinforced unsaturated polyester, surface resistance: $< 10^9 \Omega$, all-round foamed-in silicone seal
Mounting plate: Carbon steel, zinc-plated

Color: RAL 9011

**Protection category
IP to IEC 60 529:** IP 66

Certificates: IEC Ex PTB 10.0011U: yes
PTB 03 ATEX 1011U: yes

Supply includes: Housing
Door
Mounting plate

Base material: Plastic

Product features

Dimensions: Height: 600 mm (24 ")
Width: 400 mm (16 ")
Depth: 200 mm (7.9 ")

Mounting plate:	Height: 550 mm (22 ") Width: 345 mm (14 ")
Number of cam locks:	2
Lock version:	Cam
No. of locks:	2
Lock Insert:	3 mm double-bit
Packaging unit:	1 pc(s).
Weight/packaging unit:	11.5 kg (25.4 lb.)
EAN:	4028177138339
Customs tariff number:	94037000
ETIM 6.0:	EC002503
ETIM 5.0:	EC002503
eCl@ss 8.0/8.1:	27180502
eCl@ss 7.0/7.1:	27180502
eCl@ss 6.0/6.1:	27180502
eCl@ss 5.1/5.1.4:	27180502
Product description (long):	KEL Ex enclosure, WHD: 400x600x200 mm, fibreglass-reinforced unsaturated polyester, with mounting plate, Empty enclosure with hinged door
Approvals	
Approvals:	ATEX
Certificates:	EAC Ex Protection category
Declarations:	Manufacturer's declaration