



Representative

Project: Denver Water
Location: Denver

Guarantee Electric

Catalog Number: 5261
Product ID: 7TAD012060R0000
UPC Number: 78621005261
EAN Number: 05414363075509
Status: Active

Liquidtight Sealing Gasket, 3/8 Inch, with 316 Stainless Steel Retainer and Santoprene Sealing Material

- Design locks resilient sealing material in stainless steel.
- Stainless steel retainer protects seal from extruding out under torque and limits compression to an optimum predetermined value; provides high quality seal.
- Resilient material flows and seals rough edges.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Sealing Gaskets
Application	When used with an externally threaded connector provides a tight seal against oil, fumes or moisture at the knockout opening.
Standard	UL E13938, CSA
Size	3/8 Inch
Material	Stainless Steel

European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	O-ring
Material	Other
Fitting for thread size NPT	0.375

Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	100
Outer Dimensions (inches)	6.5x3.75x3.13
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001558

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321

