



Actual

Catalog Number: RAD18-188A
Product ID: 7TAI029710R0031
UPC Number: 78621076988
EAN Number: 05414363934066
Status: Active

Nylon Fully Insulated 90 Degree Flag Female Disconnect, Length .74 Inches, Width .59 Inches, Maximum Insulation .150, Tab Size .187x.020, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated

- Quick, reliable method of connection to terminal blocks and boards without the use of tools.
- Unique construction of the female disconnect offers long-term dependability.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RAD1887F

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Red
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Fully Insulated
Colour insulation	Red
Material insulation	PA
Material	Copper

Packaging

Inner Quantity	50
Inner Dimensions (inches)	2.09x1.1x3
Outer Quantity	250
Outer Dimensions (inches)	10.5x8.75x7.25
Weight Uom	4.38 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com