



*Powering Business Worldwide*

[pe.eaton.com](http://pe.eaton.com)

## 22.5 mm, Non-metallic Heavy-Duty Pushbutton Operator

E22PB6L

UPC:782113627052

### Dimensions:

- **Height:** 1 IN
- **Length:** 2 IN
- **Width:** 2 IN

**Weight:** .05 LB

**Notes:** Maximum of 3 contact blocks (6 circuits) when used with supplied 3-way adapter and optional operator plug. Suitable for external mechanical reset of overload relays. Push rod must be cut to desired length.

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Flush, with mechanical push rod
- **Actuator Color:** Blue
- **Actuator Material:** Plastic
- **Bezel:** Black
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Non-illuminated
- **Light Unit Type:** No light unit
- **Operating Mode:** Momentary
- **Size:** 25 mm
- **Series:** E22

### Supporting documents:

- [Pushbuttons](#), [Indicating lights](#), [Selector switches](#) and [Stacklights](#)



- [Eaton Specification Sheet - E22PB6L](#)

**Certifications:**

- CSA Certified
- IEC 947-5-1 MTTA
- UL 508
- Lloyd's Register Certified

**Product compliance:**

- CE Marked