



Porcelain Terminal Blocks



SPECIFICATIONS	
INSERTS:	NICKEL PLATED BRASS
HOUSING:	CERAMIC (GLAZED OPTION)
TEMP.:	500°C (HOUSING), 350°C (INSERTS)
SCREWS:	GALVANISED STEEL
STANDARD:	CE (BS EN 60998)
COLOR:	WHITE
FEATURE:	HARD & SOLID VERY HIGH TEMPERATURE NON-INFLAMMABLE RESISTANT TO CHEMICALS

RS CODE	CROSS SECTION	CURRENT RANGE	RATED VOLTAGE	DIMENSIONS (mm)						
				W	L	Φ1	Φ2	D	d	H
703-3846	4 mm ²	5-32A	450V	18	21	3.2	4.5	12	8	16
703-3855	4 mm ²	5-32A	450V	18	33	3.2	4.5	12	8	16
703-3858	10 mm ²	15-57A	450V	21	24	4.3	4.8	14	10	20
703-3852	10 mm ²	15-57A	450V	21	36	4.3	4.8	14	10	20
703-3861	16 mm ²	30-76A	450V	27	31	6.1	5.0	17	12	22
703-3864	16 mm ²	30-76A	450V	27	48	6.1	5.0	17	12	22
Cross Section:	rated for rigid wire and cables (if for flexible wire, it should be reduced one-step, i.e. 6mm ² is 4mm ²) Φ1 wire entry hole diameter Φ2 fixing hole diameter									