









## ZIF Connectors



	Plug		Receptacle		Junction Shell	
						
Number of Contacts	Stock_No	MPN	Stock_No	MPN	Stock_No	MPN
60	129-6094	DL3-60P (110900-0008)	295-3495	DL3-60R (086-0032-000)	-	DL3-J/S (249-2060-000)
96	406-616	DL2-96P (110777-0000)	406-638	DL2-96R (086-0031-000)	406-688	DL2-J/S (249-1985-000)
156	406-622	DL1-156P (110535-0000)	406-644	DL1-156R (086-0030-000)	406-694	DL-1-J/S (249-1950-000)
260	406-739	DL5-260P (111986-0014)	406-745	DL5-260R (086-4501-000)	-	-

	Plug		Receptacle		Junction Shell	
						
Number of Contacts	Stock_No	MPN	Stock_No	MPN	Stock_No	MPN
60	341-8943	DLM3-60P (127050-0220)	341-8971	DLM3-60R (127050-0224)	-	DL3/DLM3 (249-4518-000)
96	341-8959	DLM2-96P (127050-0212)	341-8987	DLM2-96R (127050-0216)	341-9019	DL2/DLM2 (249-4517-000)
156	341-8965	DLM1-156P (127050-0204)	341-8993	DLM1-156R (127050-0208)	341-9025	DL1/DLM1 (249-4520-000)
260	295-3502	DLM5-260P (127050-0109)	295-3518	DLM5-260R (127050-0110)	406-767	DL5/DLM5 (249-4501-000)
360	295-3524	DLM6-360P (127050-0034)	295-3530	DLM6-360R (127050-0045)	295-3546	DL6/DLM6 (249-4515-000)

## Corner Polarisation Kit

60, 96, 156 and 360-way bodies		260-way bodies	
			
Stock_No	MPN	Stock_No	MPN
406-701	DL-CORNER-POL-KIT (320-0021-001)	295-3568	DL-5 POLARIZING POST (320-4502-000)

## 260 Way Shield

Plug		Receptacle	
			
Stock_No	MPN	Stock_No	MPN
406-773	DL5 P SHIELD CAN (248-4500-000)	406-789	DL5 R SHIELD CAN (248-4501-000)

## ZIF Crimp and Extraction Tool

Crimping tool		Extraction tool	
			
Stock_No	MPN	Stock_No	MPN
821-611	5628-200-55-01	406-723	CET-DL-10 (274-7029-007)

## Standard and Low Current Contacts

Plug		Receptacle		Plug and Receptacle	
					
Stock_No	MPN	Stock_No	MPN	Stock_No	MPN
295-3574	AWG 24 → 26 (030-2410-003)	295-3580	AWG 24 → 26 (030-2492-001)	484-8676	AWG 20 → 22 (030-2409-001)
295-3603	AWG 20 → 22 (030-2409-003)	295-3619	AWG 20 → 22 (030-2491-001)	484-8698	AWG 18 → 20 (030-2410-001)