

XME

LED Signal Light

**LED****IP23****Ø187**

New Large Sized LED flashing beacon! Available in three LED Colors.

FEATURES

- Extended product lifespan by using LED lights.
- Indoors allows upright, inverted, and sideways installation; outdoors allows upright installation only.
- Main body is made of a melamine baked finish with a corrosion-proof stainless steel (SUS 304) lens mounting fixture.
- Dome lens is made of superior weather-resistant and light-translucent AS resin.
- Mounting Bolts are drip-proof and made of rust-free stainless steel.
- Available Colors are Red, Amber, and Blue.

Specifications

| Model | XME-12 | XME-24 | XME-M2 |
|--------------------------------------|-----------------------------------|-------------|----------------|
| Rated Voltage | DC 12V | DC 24V | AC 100 - 230V |
| Voltage Range | DC 9.5-15V | DC 20 - 28V | AC 90 - 250V |
| Current Consumption | 0.50A | 0.23A | 0.12A |
| Operating Ambient Temperature | -30°C to +70°C | | -20°C to +60°C |
| Protection Rating | IP23 | | |
| Mounting Location | Indoor or Outdoor Use | | |
| Flash Rate | 110 ±10fpm (Triple-flash Pattern) | | |
| Certifications | RoHS | | |

How to Order

XME- -

Rated Voltage

12: DC 12V

24: DC 24V

M2: AC100 - 230V

Color

R: Red

Y: Amber

B: Blue