



ENGLISH

Datasheet

Stock No: 482-783

RS Pro Panel Mount Solder D-sub Connector Plug, 15 Way, 750 V ac/dc, 5A



Product Details

High Specification Straight

Compatible with BS9523, F0013 & Mil-24308 variants

High reliability and military performance

2.5 μm gold plated

> 500 matings

Probe proof sleeved contacts

Moisture resistant one piece insulator

56 day environment classification

Solder bucket contacts

Panel Mounting

For suitable hole cutters, refer to 'D' connector cutters (e.g. stock no. [477-8690](#))

(*Standard mounting dimensions)

Note

'Harness through' dimensions permit the connector and wiring assembly (i.e. 'D' connectors terminated with Speed-bloc™ ribbon cable, 'IDC' types or other version) to be passed through the panel aperture.



ENGLISH

Specifications

Number of Contacts	15
Gender	Male
Mounting Type	Panel Mount
Body Orientation	Straight
Housing Material	Steel
Current Rating	5A
Voltage Rating	750 V ac/dc