Zone 2

AR-078 SERIES EXPLOSION-SAFE

CE 🐼 II 3 GD; Ex nA II T4; Ex tD A22 IP65 T85°C 94/9/EC (ATEX) and 2004/108/EC (EMC) EN60079-0, EN60079-15, EN61241-0, EN61241-1

Explosion-safe Signal Light Ø60mm


Description

Explosion-safe Signal Light featuring an LED light that is versatile and energy-efficient. The vertical and horizontal cut lenses in combination with a double-reflection system enhances the LED light diffusion to create a unique, full and brilliant light. The lenses and main body are made of strong synthetic materials with characteristics to withstand harsh environments. The Signal Light can be ordered in any combination from 1 to 5 LED units with any color combination. In addition to its "continuous lighting" condition, the Signal Light can also be ordered with flashing / non-flashing functions, as well as with two super-loud alarm sounds with an 90dB (at 1m) output.

Features

- Explosion-safe for gas and dust
- Suitable for Zone 2 and Zone 22
- CE compliance in accordance to ATEX
- Full and brilliant lumination
- LED double reflection lighting system
- Different lens colors available

Dimensions



Units: mm


• From 1 to 5 tiers

- 3/4" NPT bracket for pole mount is available as an option.
- Available with "flashing/non flashing" and
- two audible buzzer alarm sounds • Ingress protection of IP65
- Wall mount or direct mount

Specifications

Explosion-safety:	C € ⟨E>⟩ II 3 GD; Ex nA II T4; Ex tD A22 IP65 T85°C		
CE conformities:	EN 60079-0, EN 60079-15, EN 61241-0, EN 61241-1		
Certification:	EC-Declaration of conformity		
Ambient Temperature:	-30 °C to +60 °C		
Ingress Protection:	IP65 to EN 60529		
Material:	ABS towerbody, polyester glassfibre reinforced base		
Lighting Source:	Multiple LEDs with double reflection system		
Acoustical Source:	Buzzer 90 dB (1m) with two different tones		
Rated Voltage:	24 V AC/DC		
Assembly position:	As desired		
Activation Time:	100%		
Module Colors Available:	Red, Amber, Green, Blue, Clear/white		
Cable:	Factory sealed cable, Ø 8 mm, length 3 meter		

CURRENT		RATINGS		
LED		BUZZER		
Signal Line Current		Signal Line Current	Inrush Current	
Red, Amber	Green, Blue, Clear	Signal Line Current	Infusit Current	
approx. 30 mA approx. 25 mA		approx. 40 mA	approx. 250 mA	



▶ Type number AR-078 0 1 /

and two Audible alarms

2

- RYGBC *Colors are arranged from top to bottom

5

Clear/White



RoHS

 (ϵ)

С