

Catalog Number: 65U
Product ID: 7TBA034060R0000
UPC Number: 78621046685
Status: Active



Representative

Copper Breakaway Single Pole In-line Street Light Kits, conductor size AWG 14-6. Fuse not Included with kit - DO NOT use Glass Fuses. Kit includes Line and Load side Housings, Metal Fuse Sockets, Assembly Dowel, Lubricant, wiper and Installation Instructions.

North American Specifications (UNSPSC)

UNSPSC	39111616 Outdoor lighting accessories
IGCC	3934 Outdoor lighting accessories
Brand Name	Blackburn
Type	Breakaway Street Light Kit. Single-Pole In-Line
Special Features	Watertight and Easy to Install. Does not Require Tape, Compound or Heat Source for Fitting. Individual Fusing Enables Separation of Kit without De-Energizing Complete Circuit. Breakaway-Style Fuse Holder Eliminates Risk of Electrical Shock. Exposed Current-Carrying Components are all Contained in Load Side of Kit. Readily Identifiable Problem Area Simplifies Maintenance.
Application	Rated 600 Volts, 30 Amp Maximum, perfect for Heavy-Duty Applications
Size	AWG Conductor Size #14-#6
Material	EPDM Rubber
Color	Black



Representative

Packaging

Inner Quantity	1
Outer Quantity	20
Weight Uom	13.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------



Representative



Representative



Representative

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com