

BU-3070-C-XX-*

(Test Lead: Dual Stackable Banana Plugs to Insulated Alligator Clips)



- The BU-3070-C-* is a test lead with dual stackable, 4mm banana plugs to .080" (2mm) stackable pin tip probes. The banana plugs mate with any standard 4mm banana jacks and are spaced at the industry standard .75" (19mm).
- Constructed with RG58/U Coax cable. Center conductor is 20 AWG (19x33) tinned copper and the shield is tinned copper braid (95% coverage). The overmold material is polypropylene. Aligator Clips are nickel plated steel
- Length: The "XX" in the model number represents the overall length in inches. Standard lengths are: 12" (30cm), 24" (61cm), 36"(.9m), 48" (1.2m) and 60" (1.5m)
- Color: The "*" in the model number represents the overmold color. Available colors are: -0 Black, -2 Red,
- Ratings: 50 Ohms, Hands free testing to 300 VRMS
- RoHS Compliant

Mueller Electric Company 1208 Massillon Rd. Ste. N-1500 Akron, OH 44306-4524

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524