


## THR\_22 Coupler for 3mm Through-hole LED



## **Technical Specifications**


Material	Nylon 6/6, Black UL 94 V-2
Temperature Specifications	
Operating Temperature	-40°C to +85°C -40°F to +185°F




These LED couplers are suitable for use with VCC FLX series flexible lightpipe assemblies, resulting in a highly efficient coupling between LED and lightpipe.

For best results use non-diffused narrow viewing angle with an output power greater than 100mcd. Suitable for all light pipe mounts and terminations using a light pipe with 2.2 mm outside diameter. Do not wave solder this part.

## **Product Dimensions**





General Tolerances  $X.X = \pm .250" (6.35mm)$   $X.XX = \pm .127" (3.23mm)$   $X.XXX = \pm .025" (0.64mm)$  $X.XXXX = \pm .013" (0.33mm)$ 

Dimensions in inches (millimeters)

## **Compliances and Approvals**



your first call for illuminated components