



Representative

Project: UNKNOWN**Location:** MIAMI**EYMAQ**

13775 SW 145 CT, MIAMI FL 33186

Catalog Number: SH610AMV
Product ID: 7TAA080240R0057
UPC Number: 78620998697
Status: Active

Side entry single post hood, NPT entry-1 Inch x 1/2 Inch

North American Specifications (UNSPSC)

UNSPSC	39121424 Terminal block covers
IGCC	4594 Terminal block covers
Brand Name	Pos-E-Kon
Type	Hoods-Standard Mount
Standard	UL E215386
Material	Die-Cast Aluminum Alloy
Finish	Epoxy Powder Coated
Temperature Rating	-40 Degrees F to +257 Degrees F

European Specifications (ETIM)

ETIM	EC000437 Housing for industrial connectors
Shape	Rectangular
Length	62.992mm
Height	65.9892mm
Width	35.9918mm
Type of housing	Other
Position cable feed	Sideways
With cable screw gland	N
With hinged lid	N
Material housing	Aluminium
Coating housing	With powder coating
Inflammability class of insulation material acc. with UL94	V0
Operation temperature	-40 - +125°C

Packaging

Outer Quantity	10
Outer Dimensions (inches)	12x5x2.75
Weight Uom	39.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com