


Model 73058 UHF Jack to Jack Adapter





Model 73058 UHF Jack to Jack Adapter

Features

- DC 300MHz bandwidth.
- Connectors are precision machined.

Materials

Center Conductor: Phosphor Bronze, Gold Plated

Connector Body: Brass, Nickel Plated

Insulators: PTFE

Specifications

Frequency Range: DC – 300MHz

Contact Resistance:

 $\begin{array}{ll} \text{Center Conductor:} & \leq 1.0 \text{ m}\Omega \\ \text{Outer Conductor:} & \leq 0.2 \text{ m}\Omega \\ \text{Insulation Reistance:} & \geq 300 \text{ M}\Omega \\ \text{Dielectric Withstand Voltage:} & 750V \end{array}$

For CE compliance, do not hold in hand when

voltages exceed 33 Vrms / 70 Vdc.

Number of Insertions: 500 cycles minimum

Ordering Information

Model: **73058**

USA: Sales: 800-490-2361

Technical Support: technicalsupport@pomonatest.com

Fax: 425-446-5844

Europe: 31-(0) 40 2675 150 **International:** 425-446-5500

Where to Buy: www.pomonaelectronics.com

All dimensions are in inches. Tolerances (except noted): $.xx = \pm .02$ " (,51 mm), $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies.